




Dual inductive sensor for valve actuators

IND3004DBPKG/0,50M

Article no longer available - archive entry

Alternative articles: IN5251

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	4
Housing	rectangular
Dimensions [mm]	40 x 26 x 26

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 3
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	1300
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	4
Real sensing range S_r [mm]	$4 \pm 10 \%$
Operating distance [mm]	0...3.25


IN5270



Dual inductive sensor for valve actuators

IND3004DBPKG/0,50M

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 26 x 26
Material		PBT
Displays / operating elements		
Display	Switching status	2 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 0.5 m, PVC; 4 x 0.34 mm²		
Connection		



	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white