
IN5290

Dual inductive sensor for valve actuators

IND2004DARKG



Product characteristics		
Electrical design		PNP/NPN
Output function		2 x normally open
Sensing range	[mm]	4
Housing		rectangular
Dimensions	[mm]	40 x 26 x 26
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		2 x normally open
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	2 x 0.8
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	1400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3

IN5290


Dual inductive sensor for valve actuators

IND2004DARKG

Hysteresis	[% of Sr]	3...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
MTTF	[years]	1229	
Mechanical data			
Weight	[g]	137.5	
Housing		rectangular	
Mounting		non-flush mountable	
Dimensions	[mm]	40 x 26 x 26	
Material		PBT; PC	
Displays / operating elements			
Display		Switching status	2 x LED, yellow
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 2 m, PVC; 4 x 0.34 mm²

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white