




Inductive sensor

IIB2022-AROG/UP/2LED/3M/PH

Article no longer available - archive entry

Alternative articles: IIS709
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	22
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5
Application		
System		Increased sensing range; optical setting aid
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		no
Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	5
Minimum load current	[mA]	5
Max. leakage current	[mA]	1



Inductive sensor

IIB2022-AROG/UP/2LED/3M/PH

Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100
Short-circuit protection		no
Overload protection		no

Monitoring range		
Sensing range	[mm]	22
Operating distance	[mm]	0...17.6
Increased sensing range		yes

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Weight	[g]	235.5
Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Material		brass white bronze coated; PBT

Displays / operating elements		
Display	Switching status	1 x LED, red
	Setting aid	1 x LED, green
Optical setting aid		yes

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

II5803




Inductive sensor

IIB2022-AROG/UP/2LED/3M/PH

Electrical connection

Cable: 3 m, PUR; 2 x 0.5 mm²

Connection



BK =

Core colors :
black