



Article no longer available - archive entry

No scale drawing available



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	22
Housing	tubular
Dimensions [mm]	Ø 30

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 10
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	50
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	22
--------------------	----



Inductive sensor

IIG3022-BPKG/US-100-DPS

Real sensing range Sr	[mm]	22 ± 10 %
Operating distance	[mm]	0...17.6

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.45 / copper: 0.4
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	

Mechanical data		
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 30
Material		brass white bronze coated; PC

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

