




Inductive sensor

IIB2012BAROG/SC/2LED/0,3m/US

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	12
Housing	Threaded type
Dimensions [mm]	M30 x 1.5

Application

System	Increased sensing range; optical setting aid
--------	--

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	5
Minimum load current [mA]	5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	no



Inductive sensor

IIB2012BAROG/SC/2LED/0,3m/US

Overload protection	no
---------------------	----

Monitoring range

Sensing range [mm]	12
Operating distance [mm]	0...9.7
Increased sensing range	yes

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	3...15

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M30 x 1.5
Thread designation	M30 x 1.5
Material	brass; sensing face: PBT; end cap: PC; PTFE coated

Displays / operating elements

Display	Switching status	1 x LED, red
	Setting aid	1 x LED, green
Optical setting aid		yes

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.3 m, PVC; 2 x 0.5 mm²

Connector: 1 x M12; coding: A




II5844



Inductive sensor

IIB2012BAROG/SC/2LED/0,3m/US

Connection



BK =

Core colors :
black