




Inductive sensor

IIB2012BAROG/SC/UP/0,5m/US

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	12
Housing	Threaded type
Dimensions [mm]	M30 x 1.5

Application

System	Increased sensing range; optical setting aid; weld coated
--------	---

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	5
Minimum load current [mA]	5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	no



Inductive sensor

IIB2012BAROG/SC/UP/0,5m/US

Overload protection	no	
Monitoring range		
Sensing range	[mm]	12
Operating distance	[mm]	0...9.7
Increased sensing range		yes
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	3...15
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	Threaded type	
Mounting	flush mountable	
Dimensions	[mm]	M30 x 1.5
Thread designation	M30 x 1.5	
Material	sensing face: PBT weld coated; brass weld coated; end cap: PC	
Displays / operating elements		
Display	Switching status	1 x LED, red
	Setting aid	1 x LED, green
Optical setting aid	yes	
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection - plug		
Cable: 0.5 m, PVC; cross-linked; 2 x 0.5 mm²		
Connector: 1 x M12; coding: A		
		



II5845



Inductive sensor

IIB2012BAROG/SC/UP/0,5m/US

Connection

