




Inductive sensor

IOC2010-ARKG/0,15M/FRONT/POLAR

Article no longer available - archive entry



- 1 fixing holes M4 reinforced
2 sensing face



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 42

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.8
Minimum load current [mA]	2
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	250
Short-circuit protection	yes



Inductive sensor

IOC2010-ARKG/0,15M/FRONT/POLAR

Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range	
Sensing range [mm]	10
Real sensing range S_r [mm]	$10 \pm 10 \%$
Operating distance [mm]	0...8.1

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch-point drift [% of S_r]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	rectangular
Mounting	flush mountable
Dimensions [mm]	26 x 26 x 42
Material	PBT



Displays / operating elements		
Display	Switching status	1 x LED, red

Remarks	
Pack quantity	1 pcs.

Electrical connection

Cable: 0.15 m, silicone; 2 x 1 mm²

Connection



Core colors :
 BN = brown
 BU = blue