


IS5077



Inductive sensor

IS-2003-FRKG/0,3M/PH



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / closed; (configurable)
Sensing range	[mm]	3
Housing		rectangular
Dimensions	[mm]	28 x 10 x 16
Application		
System		Increased sensing range
Electrical data		
Operating voltage	[V]	5...36 DC
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	4.6
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	3
Real sensing range Sr	[mm]	3 ± 10 %

IS5077



Inductive sensor

IS-2003-FRKG/0,3M/PH

Operating distance	[mm]	0...2.4
Increased sensing range		yes
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	2470
UL approval	Ta	-25...75 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight	[g]	14.9
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	28 x 10 x 16
Material		PBT
Tightening torque	[Nm]	< 0.5; (with washer)
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

IS5077





Inductive sensor

IS-2003-FRKG/0,3M/PH

Electrical connection

Cable: 0.3 m, PUR / PVC; 2 x 0.14 mm²

Connection



BK = Core colors :
WH = black
 white