

# IT5004




## Inductive sensor

ITB3001-BNOG

Article no longer available - archive entry

Alternative articles: IT5008

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	1
Housing	tubular
Dimensions [mm]	Ø 6.5 / L = 35

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Reverse polarity protection	no

### Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	900
Short-circuit protection	no
Overload protection	no

### Monitoring range

Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Operating distance [mm]	0...0.8

### Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10


# IT5004



## Inductive sensor

ITB3001-BNOG

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		tubular
Mounting		flush mountable
Dimensions	[mm]	Ø 6.5 / L = 35
Material		brass nickel-plated; PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Mounting clamp: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.14 mm²		
Connection		



BN = Core colors :  
BU = brown  
BK = blue  
BK = black