




Inductive sensor

IIB3010-BNOG/MS/ 6m

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	10
Housing	Threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	18...36 DC
Current consumption [mA]	10; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	300
Short-circuit protection	no
Overload protection	no

Monitoring range


Sensing range [mm]	10
Real sensing range Sr [mm]	$10 \pm 10 \%$
Operating distance [mm]	0...8.1



Inductive sensor

IIB3010-BNOG/MS/ 6m

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		Threaded type	
Mounting		flush mountable	
Dimensions		[mm]	M30 x 1.5
Thread designation		M30 x 1.5	
Material		brass nickel-plated; PBT	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Cable: 6 m, PVC; 3 x 0.5 mm²			
Connection			



Core colors :

BN = brown

BU = blue

BK = black