

IV5044




Inductive sensor

IVE4015-CPKG/US-100-DPA

Article no longer available - archive entry

Alternative articles: IV5003
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 118
Electrical data		
Operating voltage	[V]	10...60 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary



Inductive sensor

IVE4015-CPKG/US-100-DPA

Max. voltage drop switching output DC	[V]	3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	150
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...50
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 40 x 118
Material		PBT

Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Remarks		
Remarks		5 positions of the active zone possible
		cable gland (E11270) to be ordered separately
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



IV5044



Inductive sensor

IVE4015-CPKG/US-100-DPA

Connection

