



Inductive sensor

IW-3005-BNOG

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	5
Housing	rectangular
Dimensions [mm]	60 x 36 x 10

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	200
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	5
--------------------	---

IW5003



Inductive sensor

IW-3005-BNOG

Real sensing range S_r	[mm]	$5 \pm 10 \%$
Operating distance	[mm]	0...4.05

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of S_r]	1...15
Switch-point drift	[% of S_r]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	60 x 36 x 10
Material		PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.14 mm²

Connection



Core colors :
BN = brown
BU = blue
BK = black