


Inductive sensor

IYB20,8-AROG

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	0.8
Housing	Threaded type
Dimensions [mm]	M5 x 0.5 / L = 30

Electrical data

Operating voltage [V]	10...36 DC
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	0.8
Real sensing range S_r [mm]	$0.8 \pm 10\%$
Operating distance [mm]	0...0.65

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch-point drift [% of S_r]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

IY5030



Inductive sensor

IYB20,8-AROG

Protection	IP 65
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M5 x 0.5 / L = 30
Thread designation	M5 x 0.5
Material	stainless steel (1.4305 / 303); POM

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 2 x 0.14 mm²

Connection



BN = Core colors : brown
BU = blue