


IZ5059



Inductive sensor

IZB31.5-BNKG/AS



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	1.5
Housing	tubular
Dimensions [mm]	Ø 4 / L = 40

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	1.5
Real sensing range Sr [mm]	1.5 ± 10 %
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 65; IP 67

IZ5059



Inductive sensor

IZB31.5-BNKG/AS

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL approval number	A053
	File number UL	E174191

Mechanical data		
Weight	[g]	12.4
Housing		tubular
Mounting		flush mountable
Dimensions	[mm]	Ø 4 / L = 40
Material		housing: stainless steel (1.4305 / 303); LED window: PPSU; sensing face: POM

Displays / operating elements		
Display	Switching status	4 x 90° LED, yellow

Accessories	
Items supplied	Mounting clamp: 1

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection

