




Capacitive sensor

KB-2020-BBOA/NI

Article no longer available - archive entry

Alternative articles: KB0029

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally closed
Sensing range	[mm]	3...20
Housing		tubular
Dimensions	[mm]	Ø 34 / L = 81

Electrical data

Operating voltage	[V]	20...250 AC/DC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally closed
Max. voltage drop switching output DC	[V]	8
Max. voltage drop switching output AC	[V]	10
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.7 (110 V AC) / 1.5 (24 V DC)
Permanent current rating of switching output AC	[mA]	200; (250 (...50 °C))
Permanent current rating of switching output DC	[mA]	200; (250 (...50 °C))
Short-time current rating of switching output	[mA]	1500; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	40
Short-circuit proof		no
Overload protection		no

Monitoring range

Sensing range	[mm]	3...20
---------------	------	--------



Capacitive sensor

KB-2020-BBOA/NI

Sensing range adjustable	yes
Factory setting sensing range [mm]	20

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 65
Increased immunity	yes; (Increased immunity to conducted radio frequency interference)

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Housing	tubular
Mounting	non-flush mountable
Dimensions [mm]	Ø 34 / L = 81
Material	PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Electrical connection

Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting
---------------------	--

Accessories

Items supplied	Mounting clamp: 1 screwdriver: 1
----------------	-------------------------------------


Remarks

Remarks	Recommendation: check the unit for reliable function after a short circuit.
Pack quantity	1 pcs.

Electrical connection

Cable: 2 m, PVC; 2 x 0.5 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting

Core colors :

BN =

brown

BU =

blue