


Capacitive sensor

KB-3020-APKG/US-100-DPO

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	20
Housing	tubular
Dimensions [mm]	Ø 34

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 1
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	40
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

KB5083



Capacitive sensor

KB-3020-APKG/US-100-DPO

Monitoring range		
Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2
Accuracy / deviations		
Correction factor		glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-15...15
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34
Material		PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Mounting clamp: 1 screwdriver: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M12; coding: A		
		

KB5083



Capacitive sensor

KB-3020-APKG/US-100-DPO

Connection

