

KG5011




Capacitive sensor

KGE3008-BPKG/US-100-DPS

Article no longer available - archive entry

Alternative articles: KG5057
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	8
Housing	Threaded type
Dimensions [mm]	M18 x 1

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	< 5
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	400
Switching frequency DC [Hz]	50
Short-circuit protection	yes

KG5011



Capacitive sensor

KGE3008-BPKG/US-100-DPS

Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range	
Sensing range [mm]	8
Sensing range adjustable	yes
Factory setting sensing range [mm]	8
Real sensing range Sr [mm]	$8 \pm 10 \%$
Operating distance [mm]	0...6.5

Accuracy / deviations	
Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-15...15

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65

Tests / approvals	
EMC	EN 60947-5-2

Mechanical data	
Housing	Threaded type
Mounting	non-flush mountable
Dimensions [mm]	M18 x 1
Thread designation	M18 x 1
Material	PBT; end cap: PC

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories	
Items supplied	lock nuts: 2 screwdriver: 1

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



KG5011



Capacitive sensor

KGE3008-BPKG/US-100-DPS

Connection

