




Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	2
Housing		rectangular
Dimensions	[mm]	40 x 8 x 8
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6



Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 65	
Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	3449
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191
Mechanical data		
Weight	[g]	23.4
Housing	rectangular	
Mounting	flush mountable	
Dimensions	[mm]	40 x 8 x 8
Material	brass white bronze coated; sensing face: LCP	
Displays / operating elements		
Display	Switching status	1 x LED, red
Accessories		
Items supplied	countersunk screws: 2 x M2,5 x 12	
Remarks		
Remarks	limited voltage requirements to UL 508: electrically isolated operating voltage protected by an overcurrent device	
Pack quantity	1 pcs.	
Electrical connection - plug		
Cable: 0.31 m, PUR / PVC		
Connector: 1 x M8; coding: A; Locking: Knurled nut, rotatable		
		

IL5025



Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT

Connection

