


KI0054



Capacitive sensor

KI-2200NFBOP2T/LS100



- 1 LED ring
- 2 Programming buttons



Product characteristics		
Output function		normally open / closed; (selectable)
Sensing range	[mm]	5...40; (Programming buttons)
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 90
Application		
Installation		detection through non-metallic container wall or on bypass pipes
Media		dry bulk material; liquids
Electrical data		
Frequency AC	[Hz]	47...63
Operating voltage	[V]	30...250 AC / 20...250 DC
Protection class		II
Reverse polarity protection		yes
Measuring principle		capacitive
Outputs		
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	8
Max. voltage drop switching output AC	[V]	10
Max. leakage current	[mA]	2.5 (250 V AC) / 1.7 (110 V AC) / 1.5 (24 V DC)
Permanent current rating of switching output AC	[mA]	100; (150 (...40 °C))
Permanent current rating of switching output DC	[mA]	100; (150 (...40 °C))
Short-time current rating of switching output	[mA]	1000; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	10
Switching frequency DC	[Hz]	10
Short-circuit proof		no

KI0054



Capacitive sensor

KI-2200NFBOAP2T/LS100

Overload protection	no	
Monitoring range		
Sensing range [mm]	5...40; (Programming buttons)	
Sensing range adjustable	yes	
Factory setting sensing range [mm]	20	
Real sensing range Sr [mm]	20 ± 10 %	
Accuracy / deviations		
Correction factor	glass: 0.3 / water: 1 / ceramics: 0.2 / PVC: 0.1	
Hysteresis [% of Sr]	1...15	
Switch-point drift [% of Sr]	-20...20	
Operating conditions		
Ambient temperature [°C]	-25...80	
Note on ambient temperature	temperature of the sensing face: -25...110 °C	
Protection	IP 65; IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	321	
Mechanical data		
Weight [g]	109.8	
Housing	Threaded type	
Mounting	non-flush mountable	
Dimensions [mm]	M30 x 1.5 / L = 90	
Thread designation	M30 x 1.5	
Material	housing: PBT; Pushbuttons: TPE-U; LED window: PC	
Displays / operating elements		
Display	Switching status	1 x LED ring, yellow translucent connector indicates output status
Teach function	yes	
Electronic lock	yes	
Electrical connection		
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Remarks	Note: Check the safe functioning of the unit after a short circuit.	
Pack quantity	1 pcs.	

KI0054




Capacitive sensor

KI-2200NFBOAP2T/LS100

Electrical connection - plug

Connector: 1 x 1/2"; coding: C



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting