
## KI5038

### **Capacitive sensor**

KI-3015-FPKG/NI/SS-000-K





# C€ CK

Product characteristics		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Sensing range	[mm]	15
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 92
Electrical data		
Operating voltage	[V]	1036 DC
Current consumption	[mA]	13; (24 V)
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	40
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	012.1
Accuracy / deviations		
Correction factor		glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [	% of Sr]	115

### KI5038

#### **Capacitive sensor**

KI-3015-FPKG/NI/SS-000-K



Switch-point drift	[% of Sr]	-1515	
Operating conditions			
Ambient temperature	[°C]	-2570	
Protection		IP 65	
Increased immunity		yes; (Increased immunity to conducted radio frequency interference)	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]	769	
Mechanical data			
Weight	[g]	101.5	
Housing		Threaded type	
Mounting		non-flush mountable	
Dimensions	[mm]	$M30 \times 1.5 / L = 92$	
Thread designation		M30 x 1.5	
Material		PBT	
Displays / operating el	ements		
Display		Switching status 1 x LED, yellow	
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
<b>Electrical connection -</b>	plug		

Electrical connection - plug

Connector: 1 x valve plug type A DIN (DIN EN 175301-803)



#### Connection

