


IM5052



Inductive sensor

IME3015BFPKG/NPT RT



Product characteristics		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 120
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	250

IM5052



Inductive sensor

IME3015BFPKG/NPT RT

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range	[mm]	15	
Real sensing range Sr	[mm]	15 ± 10 %	
Operating distance	[mm]	0...12.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 65	
Tests / approvals			
EMC	EN 61000-4-2 ESD		4 kV CD
	EN 61000-4-3 HF radiated		3 V/m
	EN 61000-4-4 Burst		2 kV
	EN 61000-4-6 HF conducted		3 V
	EN 55011		class B
MTTF	[years]	1727	
Mechanical data			
Weight	[g]	195.5	
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 120	
Material		PPE	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	

IM5052



Inductive sensor

IME3015BFPKG/NPT RT

Electrical connection

terminals: ...2.5 mm²; Cable sheath: Ø 7...13 mm

Connection

