

IM5067




Inductive sensor

IMC4020BCPKG/K1/US-100-DPA

Article no longer available - archive entry

Alternative articles: IM5132
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Electrical design	PNP
Output function	complementary
Sensing range [mm]	20
Housing	rectangular
Dimensions [mm]	40 x 40 x 66
Application	
System	gold-plated contacts; correction factor = 1
Electrical data	
Operating voltage [V]	10...36 DC
Current consumption [mA]	20; (24 V)
Protection class	II
Reverse polarity protection	yes
Outputs	
Electrical design	PNP

IM5067



Inductive sensor

IMC4020BCPKG/K1/US-100-DPA

Output function		complementary	
Max. voltage drop switching output DC [V]		2.5	
Permanent current rating of switching output DC [mA]		250	
Switching frequency DC [Hz]		200	
Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range [mm]		20	
Real sensing range Sr [mm]		20 ± 10 %	
Operating distance [mm]		0...16.2	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 1.1 / brass: 1.1 / aluminum: 1.1 / copper: 1.1	
Hysteresis [% of Sr]		3...15	
Switch-point drift [% of Sr]		-10...10	
Correction factor = 1		yes	
Operating conditions			
Ambient temperature [°C]		-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Dimensions [mm]		40 x 40 x 66	
Material		housing: PPE; sensing face: PPE; end cap: PPS; clamp: PPS	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Accessories			
Items supplied		Mounting bracket: 1	
		Allen key: 1	
Remarks			
Pack quantity		1 pcs.	

IM5067



Inductive sensor

IMC4020BCPKG/K1/US-100-DPA

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

