

IM5089




Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Article no longer available - archive entry

Alternative articles: IM5125 or IM5126

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	35
Housing		rectangular
Dimensions	[mm]	40 x 40 x 62
Application		
System		gold-plated contacts; weld coated
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP



Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Output function		complementary	
Max. voltage drop switching output DC [V]		2.5	
Permanent current rating of switching output DC [mA]		250	
Switching frequency DC [Hz]		100	
Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range [mm]		35	
Real sensing range Sr [mm]		35 ± 10 %	
Operating distance [mm]		0...28.3	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis [% of Sr]		1...15	
Switch-point drift [% of Sr]		-10...10	
Operating conditions			
Ambient temperature [°C]		-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
Mechanical data			
Housing		rectangular	
Mounting		non-flush mountable	
Dimensions [mm]		40 x 40 x 62	
Material		housing: PPE; sensing face: PEI weld coated; end cap: diecast zinc; clamp: diecast zinc	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Accessories			
Items supplied		Mounting bracket: 1	
		Allen key: 1	
Remarks			
Remarks		5 positions of the active zone possible	
Pack quantity		1 pcs.	

IM5089



Inductive sensor

IMC4035-CPKG/SC/US-100-DPA

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

