


IM5142



Inductive analog sensor with IO-Link

IMC4026A2PKG/IO/US



- 1 LED yellow
- 2 LED green



Product characteristics		
Electrical design		PNP/NPN; (configurable)
Output function		normally open / closed; (configurable)
Communication interface		IO-Link
Housing		rectangular
Dimensions	[mm]	40 x 40 x 54
Electrical data		
Operating voltage	[V]	15...30 DC
Current consumption	[mA]	< 33
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN; (configurable)
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100



Inductive analog sensor with IO-Link

IMC4026A2PKG/IO/US

Analog voltage output	[V]	0...10; (linear; gradient: 0,4 V/mm; for frontal approach and for target made of mild steel: 90 x 90 x 1 mm)	
Min. load resistance	[Ω]	2000	
Short-circuit protection		yes	
Overload protection		yes	
Monitoring range			
Measuring range	[mm]	1...26	
Switch point IO-Link	[mm]	3.44...24.2	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	3...15	
Note on hysteresis		configurable	
Linearity error of analog output	[%]	± 2; (of the final value of the measuring range)	
Repeatability analog output	[%]	± 2; (of the final value of the measuring range)	
Temperature coefficient		±0,15	
	[%/K vom MEW]		
Temperature drift		± 5 %; (of the final value of the measuring range)	
Reaction times			
Response time	[ms]	< 20	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Identification and diagnosis; Multi-channel, two setpoint switching sensor, type 0 Generic Profiled Sensor; Teach Channel	
SIO mode		yes	
Required master port class		A	
Min. process cycle time	[ms]	3.2	
IO-Link process data (cyclical)	Function		bit length
	process value		16
	device status		4
	binary switching information		2
IO-Link functions (acyclical)	switching cycles counter; switch-on cycle counter; operating hours counter; internal temperature; application specific tag		
Supported DeviceIDs	Type of operation		DeviceID
	default		1206
Note	For further information please see the IODD PDF file at "Downloads"		
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	

IM5142



Inductive analog sensor with IO-Link

IMC4026A2PKG/IO/US

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF [years]		231
Embedded software included		yes
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL approval number	A026
	File number UL	E174191

Mechanical data		
Weight [g]		157
Housing		rectangular
Sensing face		5 positions selectable
Mounting		non-flush mountable
Dimensions [mm]		40 x 40 x 54
Material		PA; brass white bronze coated

Displays / operating elements		
Display	target in measuring range	1 x LED, yellow lights
	target outside measuring range	1 x LED, yellow flashing
	Power	LED, green

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A




IM5142



Inductive analog sensor with IO-Link

IMC4026A2PKG/IO/US

Connection



1	L +
2	OUT
3	L -
4	OUT / IO-Link