




Inductive sensor

IMC2015-ARKG/0,15/PUR/US

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 66
Application		
System		gold-plated contacts
Electrical data		
Operating voltage	[V]	10...55 DC
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open

IM9906



Inductive sensor

IMC2015-ARKG/0,15/PUR/US

Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	0.8
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	150
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 40 x 66
Material		housing: PBT; sensing face: PEI; clamp: PPS

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories		
Items supplied		Mounting bracket: 1
		Allen key: 1

Remarks		
Pack quantity		1 pcs.

IM9906



Inductive sensor

IMC2015-ARKG/0,15/PUR/US

Electrical connection - plug

Cable: 0.15 m, PUR

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

