


IN5410



Inductive sensor

INE3004DBPKG/SOCKET M12



Product characteristics

Electrical design	PNP
Output function	2 x normally open
Sensing range [mm]	4
Housing	rectangular
Dimensions [mm]	33 x 60 x 92

Electrical data

Operating voltage [V]	10...30 DC; (; to PELV)
Current consumption [mA]	15; (a maximum of one output is switched)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	2 x normally open
Max. voltage drop switching output DC [V]	2.5

IN5410



Inductive sensor

INE3004DBPKG/SOCKET M12

Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Valve control		24 (< 20 W)

Monitoring range

Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	1072

Mechanical data

Weight	[g]	178.5
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	33 x 60 x 92
Material		housing: PA; screws: stainless steel; washer: stainless steel

Displays / operating elements

Display	Switching status	2 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	washers: 2	
	cylinder screws: 2 x M5 x 18	

Remarks

Pack quantity		1 pcs.
---------------	--	--------

IN5410




Inductive sensor

INE3004DBPKG/SOCKET M12

Electrical connection

Terminal strip in the terminal chamber:

Connection



1: solenoid valve output

Connector: 1 x M12