




Continuous level sensor with leakage monitoring

LL0264B-B-00KVPKG/US

Article to be discontinued

For 8-wire cordsets the core colors are not standardized.
Please note the wiring of the sensor and the cordsets (see data sheet).



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 Programming buttons
- 4 housing connection flat-pin connector 6.3 mm DIN 46244
- 5 Position of the temperature measuring element



Product characteristics

Number of inputs and outputs	Number of digital outputs: 4
Probe length L [mm]	264

Application

System	gold-plated contacts
Media	hydrous coolants; oils; water; media similar to water
Dielectric constant of the medium	> 2
Cannot be used for	extremely conductive media; adhering media; granulates; bulk material; acids; alkali
Tank pressure [bar]	0.5; (when mounting with mounting accessories: E43001 - E43007, E43019)
Coolants	
Medium temperature [°C]	0...35; (LL8022 + E43100: 0...65; for water and hydrous media with temperatures > 35 °C install the unit into a climatic tube)



Continuous level sensor with leakage monitoring

LL0264B-B-00KVPKG/US


Oil		
Medium temperature	[°C]	0...70
Medium temperature short time	[°C]	0...90
Water		
Medium temperature	[°C]	0...35; (LL8022 + E43100: 0...65; for water and hydrous media with temperatures > 35 °C install the unit into a climatic tube)
Electrical data		
Operating voltage	[V]	18...30 DC; (cULus - Class 2 source required)
Current consumption	[mA]	< 60
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	3
Measuring principle		capacitive
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 4
Outputs		
Total number of outputs		4
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		4
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Short-circuit protection		yes
Type of short-circuit protection		thermal, pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	264
Active range A	[mm]	195
Inactive range I1 / I2	[mm]	53 / 15
Setting range		
Set point SP	[mm]	25...190
Reset point rP	[mm]	20...185
In steps of	[mm]	5
Hysteresis	[mm]	5
Overflow switch point OP	[mm]	69 - 82 - 94 - 106 - 118 - 130 - 143 - 155 - 167 - 179 - 191 - 204
Hysteresis, OP	[mm]	2
Temperature monitoring		
Display range	[°C]	-10...100



Continuous level sensor with leakage monitoring

LL0264B-B-00KVPKG/US

Accuracy / deviations		
Measuring error		± 5
	[% of the final value]	
Repeatability		± 2
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; SP/rP position; OP position; adjustment OP; medium selection; offset setting; Display unit; settings for leakage monitoring	
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN EN 60068-2-29	15 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	202
Mechanical data		
Weight	[g]	344.6
Dimensions	[mm]	Ø 16
Material	stainless steel (1.4301 / 304); FKM; NBR; PBT; PC; PEI; PP; TPE-V	
Materials (wetted parts)	PP	
Displays / operating elements		
Display	Display unit / status	4 x LED, green
	Switching status	4 x LED, yellow
	Level	alphanumeric display, 4-digit
	Parameter setting	alphanumeric display, 4-digit
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		



LL8022



Continuous level sensor with leakage monitoring

LL0264B-B-00KVPKG/US

Connection

