

IN5008




Inductive sensor

IN-3004-BPOG

Article no longer available - archive entry

Alternative articles: IN5129

When selecting an alternative article and accessories please note that technical data may differ!



- 1 mounting hole
2 threaded bush M3 Depth 5.8 mm



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range [mm]		4
Housing		rectangular
Dimensions [mm]		40 x 12 x 26
Electrical data		
Operating voltage [V]		10...55 DC
Current consumption [mA]		15; (24 V)
Reverse polarity protection		no
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC [V]		1
Permanent current rating of switching output DC [mA]		400
Switching frequency DC [Hz]		250
Short-circuit protection		no
Overload protection		no
Monitoring range		
Sensing range [mm]		4
Real sensing range Sr [mm]		4 ± 10 %

IN5008



Inductive sensor

IN-3004-BPOG

Operating distance	[mm]	0...3.25
--------------------	------	----------

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 12 x 26
Material		PBT

Mounting hole

Tightening torque	[Nm]	< 0.5
-------------------	------	-------

Threaded bush

Tightening torque	[Nm]	< 1.2; (when brass insert in contact with counterpart)
-------------------	------	--


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²		
------------------------------	--	--

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue