


# ME5010



## Magnetic sensor

MEK3060-BPKG/AM/G/AS



### Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	60; (referred to magnet M 4.0)
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 60

### Electrical data

Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

### Monitoring range

Sensing range [mm]	60; (referred to magnet M 4.0)
Magnetic sensitivity [mT]	1.2

### Accuracy / deviations

Hysteresis [% of Sr]	1...10
----------------------	--------

### Operating conditions

Ambient temperature [°C]	-25...75
Protection	IP 67

# ME5010



## Magnetic sensor

MEK3060-BPKG/AM/G/AS

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3	10 V/m
	EN 61000-4-4	2 kV
	EN 61000-4-5	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6	10 V
	EN 55011	class B
MTTF	[years]	1445
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	UL approval number	C022
	File number UL	E174191

Mechanical data		
Weight	[g]	17.5
Housing		Threaded type
Dimensions	[mm]	M8 x 1 / L = 60
Thread designation		M8 x 1
Material		housing: stainless steel (1.4404 / 316L); sensing face: stainless steel (1.4404 / 316L); lock nut: brass



Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

**Electrical connection - plug**

Connector: 1 x M8; coding: A



1: L+  
3: L-  
4: OUT DO (NO)  
DO: digital output; NO: normally open