

# MF5001




## Magnetic sensor

MFA3060-BPKG/US-104-DPS

Article no longer available - archive entry

Alternative articles: MFS211

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	60; (referred to magnet M 4.0)
Housing	Threaded type
Dimensions [mm]	M12 x 1 / L = 63

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

### Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

### Monitoring range

Sensing range [mm]	60; (referred to magnet M 4.0)
--------------------	--------------------------------

### Accuracy / deviations

Hysteresis [% of Sr]	1...10
Repeatability [% of Sr]	1

# MF5001



## Magnetic sensor

MFA3060-BPKG/US-104-DPS

### Operating conditions

Ambient temperature	[°C]	-25...75
Protection		IP 67

### Tests / approvals

EMC	EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)

### Mechanical data

Housing		Threaded type
Dimensions	[mm]	M12 x 1 / L = 63
Thread designation		M12 x 1
Material		brass nickel-plated; sensing face: plastics

### Displays / operating elements


Display	Switching status	4 x LED, yellow
---------	------------------	-----------------

### Remarks

Pack quantity		1 pcs.
---------------	--	--------

### Electrical connection - plug

Connector: 1 x M12; coding: A



### Connection

