




Inductive sensor

IOC2010-ARKG/0,80M/US/LATERAL

Article no longer available - archive entry

Alternative articles: IO9917

When selecting an alternative article and accessories please note that technical data may differ!



- 1 fixing holes M4 reinforced
2 sensing face



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 42

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.5
Minimum load current [mA]	4
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100

IO9913



Inductive sensor

IOC2010-ARKG/0,80M/US/LATERAL

Switching frequency DC	[Hz]	250
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Sensing face		side
Mounting		flush mountable
Dimensions	[mm]	26 x 26 x 42
Material		PBT

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Cable: 0.8 m, PUR

Connector: 1 x M12; coding: A



IO9913



Inductive sensor

IOC2010-ARKG/0,80M/US/LATERAL

Connection

