


MK5027



Cylinder sensor for integrated profile cylinders

MKP3000-BPKG/US-100-DPS

Article no longer available - archive entry



1 sensing face



Product characteristics		
Electrical design		PNP
Output function		normally open
Dimensions	[mm]	41 x 30 x 27
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10
Reverse polarity protection		yes
Max. power-on delay time	[ms]	2
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	300
Switching frequency DC	[Hz]	5000

MK5027



Cylinder sensor for integrated profile cylinders

MKP3000-BPKG/US-100-DPS

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Magnetic sensitivity	[mT]	2	
Travel speed	[m/s]	< 5	
Accuracy / deviations			
Hysteresis	[mm]	1	
Repeatability	[mm]	0.1	
Operating conditions			
Ambient temperature	[°C]	-25...75	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)	
Mechanical data			
Sensing face		front	
Cylinder type		integrated profile cylinders; (Joucomatic)	
Dimensions	[mm]	41 x 30 x 27	
Material		aluminum; plastics	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			
Connector: 1 x M12; coding: A			



MK5027



Cylinder sensor for integrated profile cylinders

MKP3000-BPKG/US-100-DPS

Connection

