

MK5120




T-slot cylinder sensor

MKT2028BARKG/G/0,3M/ZH/US

Article no longer available - archive entry

Alternative articles: MK5186

When selecting an alternative article and accessories please note that technical data may differ!



- 1 Fastening clamp
2 sensing face



Product characteristics

Electrical design	NPN
Output function	normally open
Dimensions [mm]	25 x 5 x 6.5

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	30

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10000
Short-circuit protection	yes
Overload protection	yes

MK5120



T-slot cylinder sensor

MKT2028BARKG/G/0,3M/ZH/US

Monitoring range		
Magnetic sensitivity	[mT]	2.8
Travel speed	[m/s]	> 10
Accuracy / deviations		
Hysteresis	[mm]	< 1.5
Repeatability	[mm]	< 0.2
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 65; IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Mechanical data		
Weight	[g]	0.021
Mounting		flush mountable
Type of mounting		fastening clamp with combined slot / hexagon socket, width across flats 1.5
Cylinder type		T-slot cylinders
Dimensions	[mm]	25 x 5 x 6.5
Material		housing: PA; Fastening clamp: stainless steel
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		rubber memory stop: 1
		cable clip: 1
Remarks		
Remarks		cULus - Class 2 source required
Pack quantity		1 pcs.
Electrical connection - plug		
Cable: 0.3 m, PVC		
Connector: 1 x M12; coding: A; Locking: Hexagon nut, rotatable, stainless steel		

MK5120

T-slot cylinder sensor

MKT2028BARKG/G/0,3M/ZH/US



Connection

