




Inductive sensor

IS-2002-FROG/0.15m/US100IRF



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Sensing range [mm]	2
Housing	rectangular
Dimensions [mm]	28 x 10 x 16

Electrical data

Operating voltage [V]	5...36 DC
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10 \%$
Operating distance [mm]	0...1.6

Accuracy / deviations

Hysteresis [% of S_r]	3...15
Switch-point drift [% of S_r]	-10...20

IS8503



Inductive sensor

IS-2002-FROG/0.15m/US100IRF

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight	[g]	22.68
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	28 x 10 x 16
Material		PBT
Tightening torque	[Nm]	< 0.5; (with washer)
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Cable: 0.15 m, PUR / PVC

Connector: 1 x M12; coding: A

