

IT5013




Inductive sensor

ITB3001-BPOG/AS-500-DPS

Article no longer available - archive entry

Alternative articles: IT5021

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range	[mm]	1
Housing		tubular
Dimensions	[mm]	Ø 6.5

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	10; (24 V)
Reverse polarity protection		no

Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	900
Short-circuit protection		no
Overload protection		no

Monitoring range

Sensing range	[mm]	1
---------------	------	---



Inductive sensor

ITB3001-BPOG/AS-500-DPS

Real sensing range S_r	[mm]	$1 \pm 10 \%$
Operating distance	[mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of S_r]	1...15
Switch-point drift	[% of S_r]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Mechanical data

Housing		tubular
Mounting		flush mountable
Dimensions	[mm]	Ø 6.5
Material		brass nickel-plated; PBT

Displays / operating elements

Display	Switching status	1 x LED, red
---------	------------------	--------------

Accessories

Items supplied	Mounting clamp: 1
----------------	-------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection

