


MQ2005



Magnetic sensor

MQ23005BFRKG/B/AM/IO/0,3M/ZH/US



- 1 LED yellow
- 2 LED green



Product characteristics

Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)
Sensing range [mm]	5
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	20 x 8 x 32

Application

Media	Ferrous only
-------	--------------

Electrical data

Operating voltage [V]	10...30 DC
Rated insulation voltage [V]	60
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 0.3

MQ2005



Magnetic sensor

MQ23005BFRKG/B/AM/IO/0,3M/ZH/US

Outputs		
Electrical design	PNP/NPN; (configurable)	
Output function	normally open / closed; (configurable)	
Max. voltage drop switching output DC [V]	2.5	
Max. leakage current [mA]	0.1	
Permanent current rating of switching output DC [mA]	100	
Short-time current rating of switching output [mA]	100	
Switching frequency DC [Hz]	200	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Monitoring range		
Sensing range [mm]	5	
Real sensing range Sr [mm]	5 ± 10 %	
Operating distance [mm]	0...4.05	
Accuracy / deviations		
Correction factor	steel: 1	
Hysteresis [% of Sr]	< 10	
Switch-point drift [% of Sr]	-10...20	
Repeatability [% of Sr]	10	
Software / programming		
Parameter setting options	hysteresis / window; switch-off delay; switch-on operations; Auto-teach	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Identification and diagnosis; Multi-channel, two setpoint switching sensor, type 0 Generic Profiled Sensor; Teach Channel	
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	9.6	
IO-Link process data (cyclical)	Function	bit length
	process value	16
	device status	4
	binary switching information	4
IO-Link functions (acyclical)	application specific tag; operating hours counter; switching cycles counter	
Supported DeviceIDs	Type of operation	DeviceID
	default	830
Note	For further information please see the IODD PDF file at "Downloads"	
Operating conditions		
Ambient temperature [°C]	-25...80	

MQ2005



Magnetic sensor

MQ23005BFRKG/B/AM/IO/0,3M/ZH/US

Storage temperature	[°C]	-30...85
Protection		IP 65; IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles per frequency; 1 octave per minute in 3 axes
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
MTTF	[years]	1976
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL approval number	C010
	File number UL	E174191

Mechanical data

Weight	[g]	44.9
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	20 x 8 x 32
Material		diecast zinc; LED window: TPU (urethane); potting: PUR

Displays / operating elements

Display	Display operation	1 x LED, green
	Switching status	1 x LED, yellow



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 0.3 m, PUR, Ø 4.9 mm; flame-retardant (IEC 60332-2, UL: FT2)

Connection



MQ2005



Magnetic sensor

MQ23005BFRKG/B/AM/IO/0,3M/ZH/US

Connector: 1 x M12; coding: A; Locking: Knurled nut, rotatable

