




Inductive NAMUR sensor

IEA2001-N/6m PPU

Article no longer available - archive entry

Alternative articles: NE5012

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally closed
Sensing range	[mm]	1
Housing		Threaded type
Dimensions	[mm]	M8 x 1 / L = 30

Electrical data

Nominal voltage DC	[V]	8.2; (1k Ω)
Supply voltage DC	[V]	5...25
Current consumption	[mA]	< 1; (disabled; conductive: > 2,1)

Outputs

Output function		normally closed
Max. cable resistance	[Ω]	50
Switching frequency DC	[Hz]	2000

Monitoring range

Sensing range	[mm]	1
---------------	------	---

Operating conditions

Ambient temperature	[°C]	-20...70
Protection		IP 67

Tests / approvals

Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)
----------------------------	--	--------------------------------

Safety classification

Max. internal capacitance	[nF]	80
Max. internal inductance	[μ H]	110

Mechanical data

Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 30
Thread designation		M8 x 1

NE5007



Inductive NAMUR sensor

IEA2001-N/6m PPU

Material	brass nickel-plated; PBT
----------	--------------------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PUR / PVC; 2 x 0.14 mm²

Connection



BN = Core colors :
BU = brown
blue