




Inductive sensor

IVE3015-BPKG Elektronikteil

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 118
Electrical data		
Operating voltage	[V]	10...60 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	150

IV5031



Inductive sensor

IVE3015-BPKG Elektronikteil

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range	[mm]	15	
Real sensing range Sr	[mm]	15 ± 10 %	
Operating distance	[mm]	0...12.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Type of mounting		for mounting base; (E10228)	
Dimensions	[mm]	40 x 40 x 118	
Material		PBT	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Remarks			
Remarks		5 positions of the active zone possible	
		cable gland (E11270) to be ordered separately	
Pack quantity		1 pcs.	

IV5031



Inductive sensor

IVE3015-BPKG Elektronikteil

Electrical connection

Mounting base: ...2.5 mm²

Connection

