




Inductive sensor

IVE4020BCPKG/10M

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	20
Housing		rectangular
Dimensions	[mm]	40 x 40 x 128
Electrical data		
Operating voltage	[V]	10...60 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	150

IV5051



Inductive sensor

IVE4020BCPKG/10M

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range	[mm]	20	
Real sensing range Sr	[mm]	20 ± 10 %	
Operating distance	[mm]	0...16.2	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 128	
Material		PBT; sealing: FKM	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Remarks			
Remarks		5 positions of the active zone possible cable gland (E11270) to be ordered separately	
Pack quantity		1 pcs.	

IV5051




Inductive sensor

IVE4020BCPKG/10M

Electrical connection

Cable: 10 m, oil-resistant flexible cable; 4 x 0.5 mm²

Connection



BK =	Core colors :
BN =	black
BU =	brown
WH =	blue
	white