


O2I400



1D / 2D code readers

O2ICRDKG/E1/IO/EF/TB/S



- 1 lens
- 2 Illumination unit



Product characteristics		
Type of light		RGBW
Image resolution	[px]	1280 x 960
Max. reading rate	[Hz]	40
Application		
System		polarization filter
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 400; (18 V typical)
Max. current consumption	[mA]	800; (18 V with switched outputs memory stick active)
Protection class		III

O2I400



1D / 2D code readers

O2ICRDKG/E1/IO/EF/TB/S

Reverse polarity protection	yes			
Type of light	RGBW			
Wave length [nm]	625; 525; 453			
Image sensor	CMOS image sensor black/white			
Inputs / outputs				
Number of inputs and outputs	Number of digital inputs: 1; Number of digital outputs: 2			
Inputs				
Trigger	external; 24 V PNP/NPN (IEC 61131-2 Typ 3); internal			
Number of digital inputs	1			
Outputs				
Total number of outputs	2			
Electrical design	PNP/NPN; (configurable)			
Number of digital outputs	2; (configurable)			
Output function	configurable			
Max. voltage drop switching output DC [V]	2			
Max. current load per output [mA]	100			
Short-circuit protection	yes			
Type of short-circuit protection	yes (non-latching)			
Overload protection	yes			
Monitoring range				
Field of view size [mm]	Operating distance	Field of view		
	85	28 x 21		
	300	92 x 69		
	500	152 x 114		
	1000	302 x 227		
Operating distance [mm]	> 85			
Image resolution [px]	1280 x 960			
Lens type	standard			
Readable codes	Interleaved 2-of-5; Industrial 2-of-5; Code 39; Code 93; Code 128; Pharmacode; Codabar; EAN8; EAN8 Add-On 2; EAN8 Add-On 5; EAN13; EAN13 Add-On 2; EAN13 Add-On 5; UPC-A; UPC-A Add-On 2; UPC-A Add-On 5; UPC-E; UPC-E Add-On 2; UPC-E Add-On 5; GS1 DataBar Omnidirectional; GS1 DataBar Truncated; GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; GS1 DataBar Limited; GS1 DataBar Expanded; GS1 DataBar Expanded Stacked; GS1 - 128; MSI Barcode; ECC200; PDF-417; QR; Micro-QR; Aztec Code; GS1 ECC200; GS1 QR Code; GS1 Aztec Code			
Code quality based on			ISO / IEC 15415	
			ISO / IEC 15416	
			AIM DPM	
			ISO/IEC TR 29158	
			SEMI T10	
Legible fonts	Industrial; Document; OCR-A; OCR-B; Pharma; Semi; Universal; Dot Print			
Polarization filter available	yes			
Omnidirectional reading	yes			
Max. inclination to the image plane [°]	45			

O2I400



1D / 2D code readers

O2ICRDKG/E1/IO/EF/TB/S

Max. reading rate	[Hz]	40	
Software / programming			
Parameter setting options		teach button; via PC with ifm Vision Assistant	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM3 (230,4 kBaud)	
IO-Link revision		1.1	
Required master port class		A	
Supported DeviceIDs		Type of operation	DeviceID
		default	1699
Ethernet			
Number of Ethernet interfaces		1	
Transmission standard		10Base-T; 100Base-TX	
Transmission rate		10 MBit/s; 100 MBit/s	
Protocol		TCP/IP	
Factory settings		IP address: 192.168.0.69	
		subnet mask: 255.255.255.0 (Class C)	
		gateway IP address: 192.168.0.201	
		MAC address: see type label	
Usage type		Parameter setting	
Operating conditions			
Ambient temperature	[°C]	-10...50	
Storage temperature	[°C]	-40...70	
Max. relative air humidity	[%]	90; (non condensing)	
Max. height above sea level	[m]	4000	
Protection		IP 65	
Degree of soiling		3	
Tests / approvals			
EMC		EN IEC 61000-6-4 radiation of interference	industrial environments
		EN IEC 61000-6-2 noise immunity	industrial environments
Shock resistance		EN 60068-2-27	50 g 11 ms / not repetitive
		EN 60068-2-27	40 g 6 ms / repetitive
Vibration resistance		EN 60068-2-6	2 g (10 ... 150 Hz)
Photobiological safety		risk group 1; (EN 62471)	
Electrical safety		EN IEC 61010-2-201	electrical supply only via PELV circuits
Mechanical data			
Weight	[g]	592	
Type of mounting		screw mounting; (bore hole M4 x 7 mm)	
Dimensions	[mm]	45 x 45 x 86	
Material		housing: diecast zinc powder-coated; front lens: PMMA; LED window: PC; pushbuttons: POM	
Sealing material		FKM	
Tightening torque	[Nm]	2.1	

O2I400



1D / 2D code readers

O2ICRDKG/E1/IO/EF/TB/S

Displays / operating elements

Display	Function	2 x LED, green
	Function	2 x LED, yellow
	Teach-Funktion	1 x LED, green
	Teach-Funktion	1 x LED, yellow
Operating elements	1 x	Teach-Taste

Accessories

Accessories (optional)	Operating software
	Mounting accessories
	Adapter cable
	protective and filter windows

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Electrical connection - Ethernet


Connector: 1 x M12; coding: D; Moulded body: stainless steel; sealing: FKM



1	TxD+
2	RxD+
3	TxD-
4	RxD-

Electrical connection - supply

Connector: 1 x M12; coding: A; Moulded body: stainless steel



1	U+
2	trigger input
3	0 V
4	Switching output 1 configurable / IO-Link
5	Switching output 2 configurable / trigger output with external illumination