


IZ5061



Inductive sensor

IZB31,5-BPKG/2m



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1.5
Housing	tubular
Dimensions [mm]	Ø 4 / L = 25

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	1.5
Real sensing range Sr [mm]	1.5 ± 10 %
Operating distance [mm]	0...1.2

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions


Ambient temperature [°C]	-25...70
Protection	IP 65; IP 67

IZ5061



Inductive sensor

IZB31,5-BPKG/2m

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Mechanical data		
Weight	[g]	25
Housing		tubular
Mounting		flush mountable
Dimensions	[mm]	Ø 4 / L = 25
Material		housing: stainless steel (1.4305 / 303); sensing face: POM; LED ring: PA
Displays / operating elements		
Display	Switching status	1 x LED ring, yellow translucent cable entry signals output status
Accessories		
Items supplied		mounting clamps: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PUR; 3 x 0.08 mm ²		
Connection		
		
BN :	brown	
BK:	black	
BU:	blue	
BN:	L+	
BK:	OUT DO (NO)	
BU:	L-	