


O7H200



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS



Receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

System	Background suppression
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...30 DC; (UL - Class 2 source required)
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633

Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	750
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)

Monitoring range

Range	[mm]	5...30; (white paper 200 x 200 mm)
Range on white object (90 % remission)	[mm]	5...30



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS

Range on grey object (18 % remission) [mm]	6...30
Range on black object (6 % remission) [mm]	7...29
Range adjustable	no
Max. light spot diameter [mm]	2.5
Light spot dimensions refer to	at maximum range
Background suppression available	yes

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	1610

Mechanical data

Weight [g]	14.4
Housing	rectangular
Dimensions [mm]	20.3 x 15 x 9
Material	PA
Lens material	PMMA
Lens alignment	Side sensing

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm²

Connector: 1 x M8; coding: A; Locking: snap-fit



O7H200



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS

Connection

