



Diffuse reflection sensors with background suppression

O7H-HPKG/2M/PH



Receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

System	Background suppression
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	20; ((24 V))
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	633

Outputs

Electrical design	PNP
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	750
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)

Monitoring range

Range [mm]	3...100; (white paper 200 x 200 mm)
Range on white object (90 % remission) [mm]	3...100



Diffuse reflection sensors with background suppression

O7H-HPKG/2M/PH

Range on grey object (18 % remission) [mm]	6...80
Range on black object (6 % remission) [mm]	7...46
Range adjustable	no
Max. light spot diameter [mm]	7
Light spot dimensions refer to	at maximum range
Background suppression available	yes

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	1610

Mechanical data

Weight [g]	31.2
Housing	rectangular
Dimensions [mm]	20.3 x 15 x 9
Material	PA
Lens material	PMMA
Lens alignment	Side sensing

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



Core colors :
 BK = black
 BN = brown
 BU = blue