


# O7P200



## Retro-reflective sensor

O7P-DPKG/0,20M/AS



Receiver in upper lens  
transmitter in lower lens



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		polarization filter
Function principle		Retro-reflective sensor
Application		For applications in robotics, assembly and handling technology
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Outputs		
Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Monitoring range		
Range referred to prismatic reflector	[m]	0.03...1; (Prismatic reflector Ø 80 E20005; Prismatic reflector 50 x 50 mm E21299)
Range adjustable		no
Max. light spot diameter	[mm]	55

# O7P200



## Retro-reflective sensor

O7P-DPKG/0,20M/AS

Light spot dimensions refer to	at maximum range
Polarization filter available	yes

### Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

### Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	1155

### Mechanical data

Weight [g]	14.4
Housing	rectangular
Dimensions [mm]	20.3 x 15 x 9
Material	housing: PA
Lens material	front lens: PMMA
Lens alignment	Side sensing
Tightening torque [Nm]	0.5

### Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

### Remarks

Remarks	UL - Class 2 source required
Pack quantity	1 pcs.

### Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm<sup>2</sup>

Connector: 1 x M8; coding: A; Contacts: 3; Locking: snap-fit



### Connection

