


O4E201



Through-beam sensor receiver

O4E-HPKG/US100



- 1 When a M5 mounting screw is used, the max. tightening torque is 2 Nm.
2 Light incidence



Product characteristics

Type of light	red light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC; (cULus - Class 2 source required)
Current consumption	[mA]	12
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	624

Outputs

Electrical design	PNP
-------------------	-----



Through-beam sensor receiver

O4E-HPKG/US100

Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Transmitter / receiver		receiver
Range	[m]	0...50
Range adjustable		no

Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67

Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	1073

Mechanical data		
Weight	[g]	117.5
Housing		rectangular
Dimensions	[mm]	74.4 x 27 x 63.8
Material		housing: PA; Front framework: stainless steel; LED window: PC
Lens material		PMMA
Lens alignment		Side sensing

Displays / operating elements		
Display	Switching status	2 x LED, yellow

Remarks		
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Through-beam sensor receiver

O4E-HPKG/US100

Connection



Diagrams and graphs

excess gain graph



x: Abstand [mm]

y: Funktionsreservefaktor