


# KF5002



## Capacitive sensor

KFA3080NBPKG/NI/US



- 1 LED 4 x 90°
- 2 potentiometer



### Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	3...12
Housing	Threaded type
Dimensions [mm]	M12 x 1 / L = 61

### Application

Media	dry bulk material; liquids
-------	----------------------------

### Electrical data

Operating voltage [V]	10...36 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 12
Protection class	III
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	50
Short-circuit proof	yes
Overload protection	yes

### Monitoring range

Sensing range [mm]	3...12
Sensing range adjustable	yes
Factory setting sensing range [mm]	8
Real sensing range Sr [mm]	8 ± 10 %

### Accuracy / deviations

Correction factor	glass: 0.6 / water: 1 / ceramics: 0.5 / PVC: 0.4
Hysteresis [% of Sr]	1...15

# KF5002



## Capacitive sensor

KFA3080NBPKG/NI/US

Switch-point drift	[% of Sr]	-20...20
--------------------	-----------	----------

### Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes

### Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	634

### Mechanical data

Weight	[g]	39.2
Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M12 x 1 / L = 61
Thread designation		M12 x 1
Material		stainless steel (1.4404 / 316L); PEEK

### Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

### Accessories

Items supplied	lock nuts: 2
----------------	--------------

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection - plug

Connector: 1 x M12; coding: A



### Connection

