


O5D152



Laser distance sensor

O5DLCNKG/US



- 1: setting pushbuttons
2: alphanumeric display 3-digit
3: Tightening torque < 2 Nm when using a mounting screw M5

Receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Laser protection class	1
Housing	rectangular

Application

System	Background suppression
--------	------------------------

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	75; (24 V)
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	650
Typ. lifetime	[h]	50000



Laser distance sensor

O5DLCNKG/US

Inputs / outputs						
Number of inputs and outputs		Number of digital outputs: 2				
Outputs						
Total number of outputs		2				
Electrical design		NPN				
Number of digital outputs		2				
Output function		normally open / closed; (complementary)				
Max. current load per output	[mA]	100				
Switching frequency DC	[Hz]	11				
Short-circuit protection		yes				
Type of short-circuit protection		yes (non-latching)				
Overload protection		yes				
Monitoring range						
Max. light spot diameter	[mm]	5				
Light spot dimensions refer to		2 m				
Detection range hysteresis	[%]	< 4				
Note on monitoring range hysteresis		black 6 % remission				
Background suppression available		yes				
Background suppression	[m]	< 20				
Measuring/setting range						
Measuring range	[m]	0.03...2				
Sampling rate	[Hz]	33				
Interfaces						
Communication interface		IO-Link				
Transmission type		COM2 (38,4 kBaud)				
IO-Link revision		1.1				
SDCI standard		IEC 61131-9				
SIO mode		yes				
Process data binary		2				
Min. process cycle time	[ms]	6.6				
Supported DeviceIDs		<table><tr><th>Type of operation</th><th>DeviceID</th></tr><tr><td>default</td><td>372</td></tr></table>	Type of operation	DeviceID	default	372
Type of operation	DeviceID					
default	372					
Operating conditions						
Ambient temperature	[°C]	-25...60				
Note on ambient temperature		at ta < -10 °C warm-up is necessary, laser is off				
Protection		IP 65; IP 67				
Max. immunity to extraneous light	[klx]	10; (on the object)				
Tests / approvals						
EMC	EN 60947-5-2					
Laser protection class	1					

O5D152



Laser distance sensor

O5DLCNKG/US

Notes on laser protection	Caution:	Laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[years]	151


Mechanical data		
Weight	[g]	76.5
Housing		rectangular
Dimensions	[mm]	56 x 18.2 x 46.8
Material		housing: PA; Front framework: stainless steel; operator interface: TPU (urethane); lens: PMMA
Lens alignment		Side sensing

Displays / operating elements		
Display	Switching status	LED, yellow Switching output PIN 4
	Power	LED, green
	Display	alphanumeric display, 3-digit
Display unit		cm


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



4: OUT / IO-Link

O5D152



Laser distance sensor

O5DLCNKG/US

Other data

Accuracy

	Accuracy			
distance	black (6 % remission)	white (90 % remission)		
0 mm	± 25 mm	± 25 mm		
500 mm	± 25 mm	± 25 mm		
1000 mm	± 25 mm	± 25 mm		
1500 mm	± 40 mm	± 30 mm		
2000 mm	± 50 mm	± 30 mm		
Extraneous light on the object		< 10 klx		

Diagrams and graphs

Hysteresis graph

