


O5H503



Diffuse reflection sensors with background suppression

O5H-FPKG/2M



- 1 Programming buttons
2 When a M5 mounting screw is used, the max. tightening torque is 2 Nm.
Receiver in upper lens
transmitter in lower lens



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
System		Background suppression
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	25
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	624
Outputs		
Electrical design		PNP



Diffuse reflection sensors with background suppression

O5H-FPKG/2M

Output function	light-on/dark-on mode; (programmable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	200	
Switching frequency DC [Hz]	1000	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	

Monitoring range		
Range [mm]	50...1800; (white paper 200 x 200 mm 90 % remission)	
Range on white object (90 % remission) [mm]	50...1800	
Range on grey object (18 % remission) [mm]	50...900	
Range on black object (6 % remission) [mm]	50...600	
Range adjustable	yes	
Max. light spot diameter [mm]	50	
Light spot dimensions refer to	Range	
Background suppression available	yes	

Operating conditions		
Ambient temperature [°C]	-25...60	
Protection	IP 67	

Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	360	

Mechanical data		
Weight [g]	142	
Housing	rectangular	
Dimensions [mm]	56 x 18.2 x 46.8	
Material	housing: PA; Front framework: stainless steel; operator interface: TPU (urethane)	
Lens material	PMMA	
Lens alignment	Side sensing	

Displays / operating elements		
Display	Switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	

Remarks		
Remarks	cULus - Class 2 source required	
Pack quantity	1 pcs.	




Diffuse reflection sensors with background suppression

O5H-FPKG/2M

Electrical connection

Cable: 2 m, PUR; 3 x 0.34 mm²

Connection



Core colors :
 BK = black
 BN = brown
 BU = blue

Diagrams and graphs




a: sensor
 b: object
 c: background
 x: distance sensor/object [mm]
 y: min. distance object/background [mm]



Diffuse reflection sensors with background suppression

O5H-FPKG/2M

Background suppression chart



x: distance sensor/object [mm]

y: min. distance object/background [mm]

1 = object black (6 % remission) , Background white (90 % remission)

2 = object grey (18 % remission) , Background white (90 % remission)

3 = object white (90 % remission) , Background white (90 % remission)