
KG5040

Capacitive sensor

KGE2008-FRKG/NI



1 potentiometer

Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / closed; (selectable)
Sensing range	[mm]	2.5...8
Housing		Threaded type
Dimensions	[mm]	M18 x 1 / L = 110
Electrical data		
Operating voltage	[V]	10...55 DC
Protection class		II
Measuring principle		capacitive
Outputs		
Electrical design		PNP/NPN
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	1
Permanent current rating of switching output DC	[mA]	200; (400 (...50 °C))
Switching frequency DC	[Hz]	50
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	2.5...8
Sensing range adjustable		yes
Factory setting sensing range	[mm]	8
Real sensing range Sr	[mm]	8 ± 10 %
Operating distance	[mm]	0...6.5

KG5040

Capacitive sensor

KGE2008-FRKG/NI

Accuracy / deviations			
Correction factor		glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-15...15	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 65	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]	497	
Mechanical data			
Weight	[g]	80.5	
Housing		Threaded type	
Mounting		non-flush mountable	
Dimensions	[mm]	M18 x 1 / L = 110	
Thread designation		M18 x 1	
Material		PBT	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
		screwdriver: 1	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

terminals: ...2.5 mm²; Cable sheath: Ø 4.5...10 mm; Cable gland: M16 X 1.5

Connection

