
# KI5052

## **Capacitive sensor**

KIE3015-FPKG/NI/55V/US-100-DPX







Product characteristics		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Sensing range	[mm]	15
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 143
Electrical data		
Operating voltage	[V]	1055 DC; (cULus - Class 2 source required)
Current consumption	[mA]	14; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	40
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	15

# KI5052

## **Capacitive sensor**

KIE3015-FPKG/NI/55V/US-100-DPX



Operating conditions						
Ambient temperature	[°C]	-2570				
Protection			IP 65			
Increased immunity		yes; (Increas	sed immunity to conducted radio frequency interference)			
Tests / approvals						
EMC		EN 60947-5-2				
MTTF	[years]		743			
Mechanical data						
Weight	[g]		146			
Housing			Threaded type			
Mounting		non-flush mountable				
Dimensions	[mm]	M30 x 1.5 / L = 143				
Thread designation		M30 x 1.5				
Material		PBT; end cap: PC				
Displays / operating elements						
Display		Switching status	1 x LED, yellow			
Accessories						
Items supplied		lock nuts: 2				
Remarks						
Pack quantity		1 pcs.				

### Electrical connection - plug

Connector: 1 x M12; coding: A



### Connection

